Peristaltic Sampling Pumps



Geopump™ Peristaltic Pumps

The Geotech Geopump™ Series I and II Peristaltic Pumps are designed for single and multi-stage pressure or vacuum pumping of liquids. They operate by mechanical peristalsis, so the sample only comes in contact with the tubing. This allows for consistent sample integrity as well as easy cleaning and replacement. The Geopump is ideally suited for field sample removal from shallow wells and all surface water sources or for laboratory use.

FEATURES

- · Exceptional field durability
- · Operate from 60 to 600 RPM
- Up to 1 liter/min. delivery rate
- Operate to a depth of 27 feet (8 meters)
- Variable speed control
- · AC only, DC only, or AC/DC combination
- Two pumping stations available, which can be piggybacked for multi-station pumping
- · Reversible flow feature for back-flushing
- Disposable and dedicated tubing means controlled costs and no decontamination issues

OPERATION

The Geotech Peristaltic Pumps operate by mechanical peristalsis, so the sample only comes in contact with the tubing. This allows for sample integrity as well as easy cleaning and replacement. With the optional stainless steel tubing weight, tubing can be lowered to a specific depth without curling or floating on the surface of the water. Geopumps operate from any external 12V DC or 120V AC power source.

SERIES I Geopump™ Peristaltic Pumps are available in AC only, DC only, or AC/DC combination. These units have one pumping station which can be piggy-backed for multi-station pumping. They have variable speeds ranging from 60 RPM to 350 RPM.

SERIES II Geopump™ Peristaltic Pumps are available in AC only, DC only, or AC/DC combination. They have two pumping stations which can also be piggy-backed for multi-station pumping. The first pumping station has a variable speed of 30 to 300 RPM and the second station 60 to 600 RPM.





Geopump™ Peristaltic Pump Series II Kit with optional easy-load II® pump head, modular battery, 5 ft. (1.5 m) tubing, carrying case and power cord



Sample collection with the Geopump™ Peristaltic Pump Series II with optional easy-load II® pump head (dispos-a-filter™ capsule sold separately)

CALL GEOTECH TODAY (800) 833-7958

Geotech Environmental Equipment, Inc.
2650 East 40th Avenue • Denver, Colorado 80205
(303) 320-4764 • (800) 833-7958 • FAX (303) 322-7242
email: sales@geotechenv.com website: www.geotechenv.com


Peristaltic Sampling Pumps



Geopump™ Peristaltic Pumps

ACCESSORIES

- · easy-load II® pump head
- · easy-load® pump head
- Silicone tubing
- Tygon tubing
- Other tubing
- · Stainless steel tubing weight
- · Custom length power cord
- Geotech Back Flushing Membrane Filter Holder
- Geotech in-line dispos-a-filter™ filter capsule
- Rechargeable battery
- · Battery charger
- Optional stainless steel rotor for pump
- Additional power cords
- · Carrying case



easy-load® Pump Heads

SPECIFICATIONS

Operating Range Suction from 27 feet (8 meters) at sea level

Principle of Operation Mechanical peristalsis

Dimensions 3.5 x 8 x 8 in. (9 x 20 x 20 cm)

Power Source Any external 12-18 V DC @ 70 watts

90-260 V AC 47-65 Hz

Power Cord 12V DC adapter cord or standard AC power cord

Power Cord Length: AC Cord 8 feet (2.4 meters)

DC Cord 15 feet (4.6 meters)

Range of Speed:

Series I 60 to 350 rpm

Series II First pumping station 30 to 300 rpm

Second pumping station 60 to 600 rpm

Speed Control Stepless variable speed control

Liquid Delivery Rate 1.67 ml per revolution

Pumping Options Pressure or vacuum (reversible flow)

Pump Head Rotor Cold rolled steel

Warranty 1 year

Basic System Kit Geopump (as specified), 5 ft. (1.5 m) of tubing,

power cord (as specified), field case, and manual

Pump Head (sold separately) Standard, easy-load®, easy-load II®



Geopump™ Modular Battery and Charger



Geopump™ Tubing Weights

CALL GEOTECH TODAY (800) 833-7958

Geotech Environmental Equipment, Inc.2650 East 40th Avenue • Denver, Colorado 80205
(303) 320-4764 • **(800) 833-7958** • FAX (303) 322-7242

email: sales@geotechenv.com website: www.geotechenv.com